




SONATEST SITESCAN D-50

Portable entry level broadband flaw detector with a full VGA display and a 50nS (Spike) 200V Pulser with 0.5dB gain resolution



SONATEST SITESCAN D-50

Portable entry level broadband flaw detector with a full VGA display and a 50nS (Spike) 200V Pulser with 0.5dB gain resolution



The SONATEST SITESCAN Flaw Detectors have always meant highly reliable, technician focused flaw detection equipment and the SITESCAN D-50 builds on that tradition. It offers end users an entry level broadband flaw detector in the popular and portable casing of the established D-Series; with a full VGA display, a 50nS (Spike) 200V, a Pulser 0.5dB gain resolution and an optional rubber boot.

Typical applications are Weld Fabrication, Corrosion Detection, Forgings & Castings and general UT inspection.

Reliable, Rugged & Robust

An instrument's ability to perform in harsh environments with proven reliability is an important aspect of flaw detector ownership and this is enhanced by the SITESCAN D-50's outstanding battery performance which is up to 10.5 hours from full charge. The SITESCAN D-50 enclosure is constructed using automotive grade impact resistant materials, offering excellent water resistance.

Explosive Testing MIL810-G standards have been passed, together with environmental testing which has confirmed the instrument fully functioning at temperatures above 55°C. The SITESCAN D-50 has a colour transfective VGA display and maximum readability is achieved through adjustable brightness and the choice of 9 colour palettes, including black-on-white LCD emulation mode.

Advanced Defect Sizing Tools as Standard

Weld and pipe inspection are major applications for the SITESCAN D-50 and they are equipped with the latest software tools for defect sizing. The use of integrated sizing software reduces analysis time and speeds inspection. Multiple standard sizing techniques are essential for service companies working to different customer standards, especially as service work becomes more international and operators are required to work to different codes.

YOUR ADVANTAGES AT A GLANCE

UT-Lity Lite Data Management Software | Key Features:

Manage calibrations & scans: View, move and manage calibrations, A-Scans, B-Scans and thickness logs on the device or PC

Custom inspection report templates: Create customised inspection report templates and export printable PDF documents

Easy cut-and-paste export: Copy data into other applications via simple cut-and-paste

File management on PC & Device: Load, store and organise files on both PC and connected flaw detector

Thickness data export: Save, analyse, colour-code and export thickness logging data to spreadsheets or asset management software

Always up to date: Update device settings, firmware and software as new versions become available

TECHNICAL INFORMATION

DISPLAY:	Colour Transflective VGA TFT-Display (640 × 480). A-Scan Area: 400 × 510 pixels (normal), 460 × 620 (FS). Colours: 9 colour options with variable brightness.
IP RATING:	IP 67
WEIGHT:	1,7 kg (battery included)
DIMENSIONS:	238 mm (L) × 172 mm (H) × 70 mm (W)
TEMPERATURE:	-10 °C to +55 °C
OPERATION:	On battery (~10.5 h)
STORAGE:	4 GB storage available for A-scans, panels, T-logs, B-logs etc. 450,000 Panels, 200,000 A-Logs, 300,000 B-Charts, 440,000 T-Logs
TEST RANGE:	1 mm to 10,000 mm
VELOCITY:	1000 - 10000 m/s continuously variable
PROBE:	0 to 1000 µs
GAIN:	0 to 110dB adjustable in 0.5, 1, 2, 6, 14 and 20dB steps
SIZING TECHNIQUES AND SOFTWARE OPTIONS INCLUDE:	— DAC (Standard) — Split DAC & DGS/AVG (Option) — TCG (Option) — Backwall Echo Attenuation (BEA) Option (requires TCG) — AWS (Option) — AVG/DGS (Option) — API (Option) — Interface Trigger (Option) — Corrosion Software (Option)



foerstergroup.com



The FOERSTER Group is represented by subsidiaries and representatives in over 60 countries worldwide. You can find a complete overview on our website.

Headquarters

Institut Dr. Foerster GmbH & Co. KG

In Laisen 70
72766 Reutlingen
Germany

+49 7121 140 0
info@foerstergroup.com

© Copyright 2026 – Copyright notice: All contents of this work, in particular texts, photographs and graphics, are protected by copyright. Unless explicitly stated otherwise, the copyright lies with Institut Dr. Foerster GmbH & Co. KG. Please contact us if you wish to use any part of this work.

Generated: 2026-09-06 10:27:47